

TECHSPEC® 40mm Dia. UV Enhanced Aluminum, λ/4 Mirror



Stock #63-172 10 TO 12 DAYS

- 1 + **₹8,048.00**

ADD TO CART

Qty 1-5
₹8,048.00
Qty 6+
₹6,438.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
40.00

Surface Flatness (P-V):
λ/4

Substrate: ☐
BOROFLOAT®

Back Surface:

Commercial Polish
Surface Quality: 60-40
Dimensional Tolerance (mm): +0.0/-0.25
Coating Specification: R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm
Coating: Enhanced Aluminum (250-700nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%): 85
Edges: Fine Ground
Thickness (mm): 4.00 ±0.25
Type: Flat Mirror
Wavelength Range (µm): 0.25 - 0.7
Wavelength Range (nm): 250 - 700
Damage Threshold, Reference: ☐ 0.5 J/cm² @ 355nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant