

[See all 6 Products in Family](#)

40mm Dia. x 200mm FL Uncoated, DCX N-K5 Lens



Stock #32-910 CLEARANCE **20+ In Stock**

[Other Coating Options](#)

- 1 + MRP ₹2,270

! Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹2,270 each
Need More?	Request Quote

Product Downloads

General

Double-Convex Lens Type:

Physical & Mechanical Properties

40.00 +0.00/-0.10 Diameter (mm):

<1 Centering (arcmin):

Center Thickness CT (mm):

8.00 ±0.10

Edge Thickness ET (mm):

6.07

Clear Aperture CA (mm):

39

Bevel:

Protective as needed

Optical Properties

Effective Focal Length EFL (mm):

200.00 @ 587.6nm

Back Focal Length BFL (mm):

197.36

Coating:

Uncoated

Substrate:

N-K5

Surface Quality:

40-20

Power (P-V) @ 632.8nm:

1.5λ

Irregularity (P-V) @ 632.8nm:

λ/4

Focal Length Tolerance (%):

±1

f#:

5.00

Numerical Aperture NA:

0.10

Wavelength Range (nm):

330 - 2500

Regulatory Compliance

Certificate of Conformance:

[View](#)

Country of Origin:

Japan

Imported By:


Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- N-K5 Substrate
- Various Anti-Reflection (AR) Coatings
- PCX and DCX Options Available

N-K5 Lenses are available in various diameters, focal lengths, as well as Plano-Convex and Double-Convex form factors. Anti-reflective coatings covering the VIS to NIR make these ideal for multiple applications.

Technical Information



Compatible Mounts