

TECHSPEC® 40mm, English Micrometer Z-Stage



TECHSPEC® Vertical Translation Stages



Stock #66-499 2 In Stock

-

1

+

₹52,079

ADD TO CART

Volume Pricing	
Qty 1-2	₹52,079 each
Qty 3+	₹45,367 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

English

Type:

Physical & Mechanical Properties

Linear (Z)	Type of Movement:
Crossed Roller Bearing	Guide System:
40 x40	Stage Size (mm):
10	Travel (mm):
1/4-20	Center Hole:
Aluminium Stage	Construction:
0.635	Leadscrew Pitch (mm):
2	Load Capacity (kg):
1.57 x 1.57	Stage Size (inches):
3	Straight Line Accuracy (µm):

Hardware & Interface Connectivity

English Micrometer	Type of Drive:	
--------------------	-----------------------	--

Threading & Mounting

Mounting Threads:
(1) 1/4-20, (4) 6-32, (8) 2-56

Regulatory Compliance

Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	REACH 241:

PRODUCT DETAILS

Bottom adapter plates, sold separately, are required to mount 30mm and 40mm stages to standard breadboards.

- Mechanically Compatible with our **TECHSPEC® Stages**
- Fine Micrometer Movement
- Locking Screw on Stages

Our newly developed precision TECHSPEC® Vertical Translations Stages (Z-axis stages) feature a unique and advanced crossed roller bearing guide system that provides high accuracy, rigidity and load capacity. Each stage is designed to integrate with our line of [TECHSPEC® stages](#) in order to provide flexibility in allowing the user to create a number of multi-axis configurations. These stages have a locking screw and fine micrometer movement. TECHSPEC® Vertical Translations Stages are constructed of aluminum and have a linear (Z) movement. The stages are available in both English and Metric versions and are offered in four sizes.

TECHNICAL INFORMATION

