

28mm Max. Aperture, Stainless Steel Iris Diaphragm



Stock #64-504 10 TO 12 DAYS

- 1 + ₹7,830.00

ADD TO CART

Qty 1-4
₹7,830.00
Qty 5+
₹6,934.00
Volume Pricing
Request Quote

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
1.5

Maximum Aperture (mm):
28.0

Outer Diameter (mm):
40.0

Construction: Blackened Brass Housing, Stainless Steel Leaves
Lever Diameter (mm): 3.00
Lever Length (mm): 12.60
Number of Leaves: 16.00
Thickness (mm): 5.50

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)
