

TECHSPEC® 4.25" Diameter x 25.5" FL Protected Aluminum, Parabolic Mirror



Stock #32-066-522

10 TO 12 DAYS

-

1

+

₹37,932.00

ADD TO CART

Qty 1-9
₹37,932.00
Qty 10+
₹32,277.00
Volume Pricing
Request Quote

Get Product Downloads

Substrate:

BOROFLOAT®

Focal Length Tolerance (%):

±1

Surface Quality:

60-40

Surface Accuracy:

λ/8

Diameter (inches): 4.25 +0.06/-0
Diameter (mm): 108.00 +1.5/-0
Effective Focal Length EFL (inches): 25.5
Effective Focal Length EFL (mm): 647.70
Radius of Curvature (mm): 1,295.40
Aperture (f/#): f/6
Coating: Protected Aluminum (400-2000nm)
Coating Specification: R _{avg} >85% @ 400 - 700nm R _{avg} >90% @ 400 - 2000nm
Coating Type: Metal
Back Surface: Ground
Clear Aperture CA (mm): 98
Edge Thickness ET (inches): 0.75
Edge Thickness ET (mm): 19.10
Type: Parabolic Mirror
Wavelength Range (μm): 0.4 - 2
Wavelength Range (nm): 400 - 2000
Damage Threshold, Reference: ☐ 0.3 J/cm² @ 532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant