

TECHSPEC® 4.25" Diameter x 34" FL Protected Gold, Parabolic Mirror



Stock **#32-067-566** [CONTACT US](#)

- 1 + **₹46,632.00**

ADD TO CART

Qty 1-9
₹46,632.00
Qty 10+
₹39,672.00
Volume Pricing
Request Quote

Get Product Downloads

Substrate: [BOROFLOAT®](#)

Focal Length Tolerance (%):
±1.5

Surface Quality:
60-40

Surface Accuracy:
λ/8

Diameter (inches): 4.25 +0.06/-0
Diameter (mm): 108.00 +1.5/-0
Effective Focal Length EFL (inches): 34.0
Effective Focal Length EFL (mm): 863.60
Radius of Curvature (mm): 1,727.20
Aperture (f/#): f/8
Coating: Protected Gold (700-10000nm)
Coating Specification: Ravg >96% @ 700 - 2000nm Ravg >96% @ 2000 - 10,000nm
Coating Type: Metal
Back Surface: Ground
Clear Aperture CA (mm): 98
Edge Thickness ET (inches): 0.75
Edge Thickness ET (mm): 19.10
Type: Parabolic Mirror
Wavelength Range (µm): 0.7 - 10
Wavelength Range (nm): 700 - 10000
Damage Threshold, Reference: 0.8 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant