

4.3mm FL, High Resolution, f/2, Micro Video Lens



Stock #88-590 10 TO 12 DAYS



1



₹6,438.00

ADD TO CART

Qty 1-49

₹6,438.00

Qty 50+

₹4,959.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Length (mm):
21.50

Maximum Diameter (mm):
22.0

Maximum Image Circle (mm):
6.60

Horizontal Field of View @ Max Sensor Format:
68

Resolution, On-Axis: 100 lp/mm @ 72.0% Contrast
Resolution, 0.7 Field: 100 lp/mm @ 56.0% Contrast
Resolution, Full Field: 100 lp/mm @ 46.0% Contrast
Note: High Resolution
TV Distortion (%): -0.4
Type: M12 Imaging Lens
Focal Length FL (mm): 4.30
Maximum Sensor Format: 1/2.7"
Working Distance (mm): 400 - ∞
Mount: M12 x 0.5 (S-Mount)
Aperture (f/#): f/2
IR Cut Filter: No
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View