

TECHSPEC®

45° Hot Mirror Mounted in C-Mount Cube



Stock #62-641 10 TO 12 DAYS

- 1 +

₹24,360.00

ADD TO CART

Qty 1+
₹24,360.00

Volume Pricing
Request Quote

Get Product Downloads

Surface Quality:
80-50

Type:
Hot Mirror

Extension Length (mm):
38.0

Dimensional Tolerance (mm):
0.5

Type of Optics:
45° Hot Miror

Coating Specification:
T_{avg} ≥85% @ 425 - 675nm
R_{avg} ≥90% @ 750 - 1125nm

Thread Type:
C-Mount (1" x32 TPI)

Coating:
Hot Mirror, 45°

Substrate: ☐
[BOROFLOAT®](#)

Filter Included:
[#62-630](#)

Regulatory Compliance

RoHS:
[Compliant](#)

Certificate of Conformance:
[View](#)
