

TECHSPEC® 45° Tip/Tilt Mount for 25/25.4mm Mirror



#85-696

Stock **#85-696 3 In Stock**

⊖ 1 ⊕ ₹15,839

● Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹15,839 each
Need More?	Request Quote

Product Downloads

General

Tip-Tilt **Function:**

Circular **Type of Optics:**

Note:
Accepts 25/25.4mm Diameter Optics Mounted at 45°

Physical & Mechanical Properties

Compatible Plate Inner Diameter (mm):
25.0

Black Anodized Aluminum **Construction:**

10 & 12 (Dual Path) **Through Hole Diameter (mm):**

25 Dia. **Dimensions (mm):**

0.5 **Adjustment Screw Pitch (mm):**

±8 Tip/Tilt **Travel (°):**

Threading & Mounting

25.0 - 25.4 **Size of Compatible Optics (mm):**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

United States **Country of Origin:**

Edmund Optics India Private Limited **Imported By:**

Product Details

- Available for a Range of Optical Components
- Anodized Aluminum Construction with Stainless Steel Screws
- 0.5mm Pitch Fine Adjustment Screw
- [Fixed Optical Mounts](#) Also Available

Ideal for beam steering applications, TECHSPEC® Cage System Adjustable Optical Mounts are used to integrate a variety of optical components into a TECHSPEC Cage System. Designed to fit within the inner diameter of 25mm or 30mm standard [cage system plates](#), these optical mounts utilize set screws to secure optical components in place, providing the stability and adjustment needed for precision optical alignment. [#85-695](#) 25.4mm Kinematic Mount features a 12.7mm clear aperture and can be paired with [#85-699](#) 45° plate beamsplitter mount.