

4.61mm FL, High Resolution, f/1.6, Micro Video Lens



Stock #11-325 10 TO 12 DAYS

- 1 +

₹6,438.00

ADD TO CART

Qty 1-49

₹6,438.00

Qty 50+

₹4,959.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Length (mm):
24.18

Maximum Diameter (mm):
19.0

Maximum Image Circle (mm):
8.00

Horizontal Field of View @ Max Sensor Format:
97.2

Resolution, On-Axis: 100 lp/mm @65.8% Contrast
Resolution, 0.7 Field: 100 lp/mm @55.9% Contrast
Resolution, Full Field: 100 lp/mm @45.8% Contrast
Note: High Resolution
TV Distortion (%): -24.9
Type: M12 Imaging Lens
Focal Length FL (mm): 4.61
Maximum Sensor Format: 1/2"
Working Distance (mm): 400 - ∞
Mount: M12 x0.5 (S-Mbunt)
Aperture (f/#): f/1.6
IR Cut Filter: Yes
Lens Wavelength Range: VIS (IR-Cut Filter)

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View