

4.6mm FL, High Resolution, f/2, Micro Video Lens



Stock #88-591 10 TO 12 DAYS

- 1 +

₹6,438.00

ADD TO CART

Qty 1-49
₹6,438.00
Qty 50+
₹4,959.00
Volume Pricing
Request Quote

Get Product Downloads

Length (mm):
13.10

Maximum Diameter (mm):
12.0

Maximum Image Circle (mm):
6.50

Horizontal Field of View @ Max Sensor Format:
71

Resolution, On-Axis: 100 lp/mm @ 72.0% Contrast
Resolution, 0.7 Field: 100 lp/mm @ 38.0% Contrast
Resolution, Full Field: 100 lp/mm @ 29.0% Contrast
Note: High Resolution
TV Distortion (%): -27.1
Type: M12 Imaging Lens
Focal Length FL (mm): 4.60
Maximum Sensor Format: 1/2.8"
Working Distance (mm): 400 - ∞
Mount: M12 x 0.5 (S-Mount)
Aperture (f/#): f/2
IR Cut Filter: No
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View