

4.6" Red Advanced Illumination High Intensity Ring Light

See More by [Advanced Illumination](#)



Stock **#88-489** [CONTACT US](#)

-

1

+

₹74,646.00

ADD TO CART

Qty 1+

₹74,646.00

Volume Pricing

[Request Quote](#)

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color:
Red

Diameter (mm):
116.80

Height (mm):
19.1

Inner Diameter (mm): M67 x0.75
Model Number: RL127-625-IC
Operating Temperature (°C): 0 to 60
Outer Diameter (mm): 116.8
Wavelength (nm): 625.00
Weight (g): 304.00
Working Distance (mm): 100 - 300
LED Lifetime (hours): 50,000
Power Supply: Power Supply Required and Sold Separately: USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Number of Channels: 1.00
Type of Illumination: LED Illuminator
Note: Optional Manual Intensity Adjustment #86-887 and #89-555 are Available
Manufacturer: Advanced Illumination
Geometry: Ring Light
Illumination Mode: Constant
Environmental Rating: IP67

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Contains SVHC(s)