

34mm Max. Aperture, Iris Diaphragm



Stock **#41-972** 10 TO 12 DAYS

-

1

+

₹8,526.00

ADD TO CART

Qty 1-4
₹8,526.00
Qty 5+
₹7,517.00
Volume Pricing
Request Quote

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
1.5

Maximum Aperture (mm):
34.0

Outer Diameter (mm):
49.0

Construction: Brass Housing, Blue Tempered Steel Leaves
Lever Diameter (mm): 3.00
Lever Length (mm): 12.00
Number of Leaves: 14.00
Thickness (mm): 6.50

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)