

4" x 4" (200 lp/inch), Ronchi Ruling



Stock #56-621 CLEARANCE **2 In Stock**

1 MRP ₹64,251

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-4	₹64,251 each
Qty 5+	₹61,118 each
Need More?	Request Quote

Product Downloads

General

English **Type:**

Physical & Mechanical Properties

Dimensional Tolerance (inches):
±0.02

Dimensions (inches):
4 x 4

Thickness (mm):

1.50

Parallelism (arcmin):

±60

Dimensional Tolerance (mm):

± 0.02

Line to Line Parallelism (arcsec):

≤2

Parallelism of Pattern to Substrate (°):

±1

Optical Properties

Coating:

Vacuum Deposited Chrome, OD >3.0

Substrate: □

Float Glass

Optical Density OD (Average):

3.00

Surface Quality:

20-10

Frequency (lp/inch):

200.00

Surface Flatness (P-V):

1λ

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 240:

[Compliant](#)

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Chrome on Glass
- High Tolerance
- Superior to Etched and Filled Rulings
- Lines Parallel to Edge
- English and Metric Versions Available

High Precision Ronchi Rulings are excellent for evaluating resolution, field distortion, and parfocal stability. The glass targets are coated with vacuum-deposited chrome and have a float glass substrate. English and Metric version are available with various Linepairs Per Inch (LPI) and Linepairs Per Millimeter (lp/mm) measurements. High Precision Ronchi Rulings are offered in 0.5", 1", 2", and 4" squares.