

4X 120mm WD, In-Line Illumination Telecentric Lens



Stock #59-838 10 TO 12 DAYS

- 1 +

₹119,190.00

ADD TO CART

Qty 1+
₹119,190.00

Volume Pricing
Request Quote

Get Product Downloads

Length (mm):
110.00

Ferrule Diameter (inches):
0.312

Horizontal Field of View, 1/2" Sensor:
1.6mm

Horizontal Field of View, 2/3" Sensor:
2.2mm

Maximum Diameter (mm):
17.0

Horizontal Field of View @ Max Sensor Format: 2.2mm
Type: Telecentric Lens
Primary Magnification PMAG: 4X
Maximum Sensor Format: 2/3"
Working Distance (mm): 120.00
Mount: C-Mount
Style: In-Line Illumination
Aperture (f/#): f/43.9
Distortion (%): ≤0.1
Compatible Light Guide/Source: 1/4" (0.312")
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Not Compliant
Certificate of Conformance: View