


[All Products](#) / [Test Targets](#) / [Distortion Test Targets](#) / [Fixed Frequency Grid Distortion Targets](#)

[See all 26 Products in Family](#)

50 x 50mm, 1.0mm Spacing, Glass Distortion Target



Stock **#62-211** [CONTACT US](#)

[-](#) 1 [+](#) **₹57,594.00**

ADD TO CART

Qty 1-4
₹57,594.00
Qty 5+
₹54,758.00
Volume Pricing
Request Quote

Get Product Downloads

Coating:
Reflective First Surface Chromium
R_{abs} = 50% ±5% @ 550nm

Dot Diameter (mm):
0.250

Dot Spacing (mm):

1.000
Substrate: Soda Lime Float Glass
Optical Density OD (Average): >3.0
Overall Accuracy (mm): ±0.002
Pattern Size (mm): 50 x 50
Dimensions (inches): 3 x 3
Surface Quality: 40-20
Thickness (mm): 1.50
Type: Chrome on Glass
Dot Diameter Tolerance (mm): ± 0.002
Dot Spacing Tolerance (mm): ± 0.002 Center to Center
NIST Certification: Serialized NIST Traceable Certificate Included
Flatness (inches): 0.001

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View
