

50 x 50mm, 40R/60T, Plate Beamsplitter



Stock #43-358 10 TO 12 DAYS

- 1 + ₹5,829.00

ADD TO CART

Qty 1-9
₹5,829.00
Qty 10+
₹4,350.00
Volume Pricing
Request Quote

Get Product Downloads



Coating Specification:
Surface 1: Dielectric, ±5% R/T @ 550nm
Surface 2: Uncoated

Construction:
Plate

Dimensional Tolerance (mm):
±0.38

Dimensions (mm): 50.0 x 50.0
Edges: Cut
Reflection/Transmission Ratio (R/T): 40/60
Substrate: Float Glass
Surface Flatness (P-V): 4 - 6λ
Surface Quality: 80-50
Thickness (mm): 1.00
Type: Standard Beamsplitter
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant