

TECHSPEC[®] 50 x 50mm, 4mm Thick UV-VIS Coated, 1λ Fused Silica Window



Stock #84-480 10 TO 12 DAYS

-

1

+

₹12,615.00

ADD TO CART

Qty 1-5
₹12,615.00
Qty 6+
₹10,092.00
Volume Pricing
Request Quote

Get Product Downloads



Abbe Number (v_d):
67.8

Bevel:
Protective as needed

Clear Aperture (%):
90

Clear Aperture CA (mm):

45.00 x 45.00
Dimensions (mm): 50.00 x 50.00
Thickness (mm): 4.00 ±0.38
Coating: UV-VIS (250-700nm)
Coating Specification: R _{abs} ≤1.0% @ 350 - 450nm R _{avg} ≤1.5% @ 250 - 700nm
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 0.52 (+5 to +35°C) 0.57 (0 to +200°C) 0.48 (-100 to +200°C)
Density (g/cm³): 2.20
Edges: Fine Ground
Index of Refraction n_d: 1.458
Knoop Hardness (kg/mm²): 522
Parallelism (arcmin): <5
Poisson's Ratio: 0.16
Substrate: Fused Silica (Corning 7980)
Surface Flatness (P-V): 1λ
Surface Quality: 60-40
Type: Protective Window
Wavelength Range (nm): 250 - 700
Young's Modulus (GPa): 73
Length (mm): 50.00
Width (mm): 50.00
Damage Threshold, Reference: ☐ 3 J/cm² @ 355nm, 10ns 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant