

50 x 75mm, Red, EuroBrite™ Backlight

See More by [Advanced Illumination](#)



AI EuroBrite Backlight



Stock **#33-457** 10 TO 12 DAYS



1



₹16,965.00

ADD TO CART

Qty 1+

₹16,965.00

Volume Pricing

[Request Quote](#)

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color:
Red

Operating Lifetime (hours):
50,000

Input Voltage (V):

24V nominal (min. 22 / max. 28)
Model Number: BL-S050075-625
Operating Temperature (°C): 0 - 60
Dimensions (mm): 75 x 89 x 30
Wavelength (nm): 625.00
Weight (g): 97.00
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Active Area (mm): 50 x 75
Type of Illumination: LED Illuminator
Note: See Technical Information Tab for Typical Intensity
Geometry: Backlight
Maximum Input Current: 0.42 - 0.49A
Analog Intensity Control: 10% @ 0.7V, 100% @ 10V
Trigger-to-Pulse Latency: 10µm
Illumination Mode: Strobed or Constant

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Contains SVHC(s)