

TECHSPEC® 50.0mm Dia. x 175.0mm FL, VIS-EXT, Inked, Plano-Convex Lens



Stock **#88-765-INK** 17 TO 22 D= DAYS

[Other Coating Options](#)

- 1 + **₹6,786.00**

ADD TO CART

Qty 1-9
₹6,786.00
Qty 10+
₹6,112.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
50.00 ±0.025

Effective Focal Length EFL (mm):
175.00 @587.6nm

Back Focal Length BFL (mm): 169.05
Coating: VIS-EXT (350-700nm)
Coating Specification: R _{avg} <0.5% @ 350 - 700nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 9.00 ±0.10
Edge Thickness ET (mm): 5.48
Radius R₁ (mm): 90.44
Clear Aperture CA (mm): 49
f/#: 3.5
Numerical Aperture NA: 0.14
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 350 - 700
Damage Threshold, By Design: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View