

50.8 x 50.8mm Right-Handed Circular Polarizing Film (CP42HER)



Stock #88-092 CLEARANCE 10 TO 12 DAYS

-

1

+

₹2,349.00

ADD TO CART

Qty 1-5
₹2,349.00
Qty 6+
₹1,914.00
Volume Pricing
Request Quote

Get Product Downloads

Substrate: [Polymer Film CP42HER](#)

Length (mm):
50.80

Operating Temperature (°C):
-40 to +80

Dimensions (mm):
50.8 x 50.8

Thickness (mm): 0.27 ±0.04
Transmission (%) : 42.00
Type: Right-Handed Circular Polarizer
Dimensional Tolerance (mm): +0.0/-0.5
Construction: Polarizing Film
Wavelength Range (nm): 400 - 700
Polarization Efficiency (%) : >99.90
Heat Resistance (°C x Hours): 80 x 500
Width (mm): 50.80
#Sorting: 20.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Contains SVHC(s)