

[See all 10 Products in Family](#)

## 50.8mm Dia., Aluminum Coated, Aluminum Substrate Mirror



Metal Substrate Mirrors

Stock **#47-117** **8 In Stock**

-

1

+

₹28,882

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | ₹28,882 each                  |
| Qty 6-25       | ₹26,002 each                  |
| Qty 26-49      | ₹24,601 each                  |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Flat Mirror

Type:

Physical & Mechanical Properties

50.80 +0.00/-0.38

Diameter (mm):

9.50

Thickness (mm):

|                                                                           |                         |
|---------------------------------------------------------------------------|-------------------------|
| 90                                                                        | Clear Aperture (%):     |
| <175                                                                      | Surface Roughness (□):  |
| Optical Properties                                                        |                         |
| 0.4 - 12                                                                  | Wavelength Range (µm):  |
| Metal                                                                     | Coating Type:           |
| Protected Aluminum (400-12000nm)                                          | Coating:                |
| 400 - 12000                                                               | Wavelength Range (nm):  |
| Aluminum 6061-T6                                                          | Substrate: □            |
| Ravg >85% @400 - 700nm<br>Ravg >70% @ 700 - 2000nm<br>Ravg >97% @2 - 12µm | Coating Specification:  |
| 80-50                                                                     | Surface Quality:        |
| λ/4                                                                       | Surface Flatness (RMS): |


|                                     |                             |
|-------------------------------------|-----------------------------|
| Threading & Mounting                |                             |
| 6-32 TPI Tapped Holes               | Mounting Threads:           |
| Regulatory Compliance               |                             |
| Compliant                           | RoHS 2015:                  |
| View                                | Certificate of Conformance: |
| Compliant                           | Reach 247:                  |
| United States                       | Country of Origin:          |
| Edmund Optics India Private Limited | Imported By:                |

Product Details

- Aluminum Substrate Mirrors
- Ideal for LWMR Laser Applications
- Aluminum and Gold Coating Options

Metal Substrate Mirrors are available with either a protected aluminum or gold coating and are ideal for LWMR (greater than 2000nm) laser applications. Due to the 17.5nm roughness of the diamond turned surface, these mirrors may not be suitable for UV and visible applications that require low scatter. The backs of the mirrors are machined flat and are tapped with 3 holes for easy, accurate mounting. Metal Substrate Mirrors are aluminum substrate, diamond turned metal mirrors. These mirrors are available in five diameters: 25.4, 38.1, 50.8, 76.2, and 101.6mm.

Technical Information



# Compatible Mounts

;