

TECHSPEC[®] 50.8mm Dia., Uncoated, Ultrafast Thin Window



Stock #11-751 10 TO 12 DAYS

-

1

+

₹16,965.00

ADD TO CART

Qty 1-5
₹16,965.00
Qty 6+
₹15,269.00
Volume Pricing
Request Quote

Get Product Downloads



Coating:
Uncoated

Diameter (mm):
50.80 +0.00/-0.10

Substrate:

Fused Silica (Corning 7980)

Index of Refraction n_d :

1.458
Surface Quality: 20-10
Thickness (mm): 1.00 ±0.10
Type: Ultrafast Window
Bevel: Protective as needed
Clear Aperture (%) : 90
Transmitted Wavefront, P-V: λ/6
Abbe Number (v_d): 67.8
Parallelism (arcsec): ≤30
Wavelength Range (nm): 200 - 2200
Fused Silica Grade: 7979 0G
Edges: Fine Ground
Type of Window: Glass

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View