

TECHSPEC[®] 50.8mm Dia. x 250.0mm EFL, Uncoated, Concave Laser Mirror



TECHSPEC Uncoated Concave Mirrors

Stock #11-350 10 TO 12 DAYS

-

1

+

₹17,400.00

ADD TO CART

Qty 1-4
₹17,400.00
Qty 5+
₹15,312.00
Volume Pricing
Request Quote

Get Product Downloads



Substrate: ☐
[Fused Silica](#) (Coming 7980)

Surface Quality:
20-10

Diameter (mm):
50.80 +0.00/-0.20

Effective Focal Length EFL (mm): 250.00
Radius of Curvature (mm): 500.00
Coating: Uncoated
Back Surface: Fine Grind
Center Thickness CT (mm): 9.35
Clear Aperture (%): 90
Edge Thickness ET (mm): 10.00 ±0.20
Radius R₁ (mm): 500.00
Type: Concave Mirror
Irregularity (P-V) @ 632.8nm: 3λ/20

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View