

50.0/50.8mm Optic Dia., 5 Axes Optical Mount



Stock #13-778 10 In Stock

-

1

+

₹57,580

ADD TO CART

Volume Pricing	
Qty 1-4	₹57,580 each
Qty 5-9	₹54,704 each
Qty 10+	₹48,946 each
Need More?	Request Quote

Product Downloads

General	
Adjustable - Linear (XYZ) & Tip-Tilt	Type:
Circular	Type of Optics:

Physical & Mechanical Properties	
46.0	Clear Aperture CA (mm):

±2.0 in X and Y, ±1.5 in Z	Travel (mm):
0.66	Weight (kg):
Black Anodized Aluminum	Construction:
±2	Tip/Tilt Angle (°):

Threading & Mounting

50.0 - 50.8	Size of Compatible Optics (mm):
12.5 (Max)	Thickness of Compatible Optics (mm):
M6 x 1.0	Compatible Post:

Regulatory Compliance

Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 247:
Japan	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- 2-Axis, 3-Axis, and 5-Axis Adjustable Mounts Available
- Options for 12.5mm (0.5"), 25mm (1"), and 50mm (2") Dia. Optics
- M6 Mounting Threads

Multi-Axis Adjustable Optic Mounts can adjust optic positioning along the X- and Y-axes, as well as through optional Z-axis and Tip/Tilt adjustment. Compact packaging allows for fine alignment adjustments without the additional use of bulkier stages. Multi-Axis Adjustable Optic Mounts are ideal for alignment adjustments in prototyping and precision laboratory benchtop optical systems. These mounts include M6 mounting threads making them compatible with our standard [Metric Stainless Steel Mounting Posts](#). A retainer ring and Delrin ring are used together to secure the optic without damaging its surface.

Technical Information

