

TECHSPEC® 50mm 850nm, Laser Line Polarizing Cube Beamsplitter



TECHSPEC Laser Line Polarizing Cube Beamsplitters

Stock **#48-868** 10 TO 12 DAYS



1



₹53,505.00

ADD TO CART

Qty 1-5
₹53,505.00
Qty 6+
₹42,108.00
Volume Pricing
Request Quote

Get Product Downloads

Beam Deviation (arcmin):
±3

Bevel:
Protective bevel as needed

Clear Aperture (%):
90.00

Coating Specification:

R _{abs} <0.25% @ 850nm
Construction: Cube
Design Wavelength DWL (nm): 850
Dimensions (mm): 50.0 x 50.0 x 50.0 ±0.1
Extinction Ratio: 1000:1
P-Polarization Transmission (%): >95
S-Polarization Reflection (%): >99.5
Substrate:  N-BK7
Surface Flatness (P-V): λ/4
Surface Quality: 40-20
Type: Linear Polarizer

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View