

50mm Dia. 750-850nm, NIR Linear Polarizer



Stock #48-894 10 TO 12 DAYS

- 1 + ₹45,675.00

ADD TO CART

Qty 1-5
₹45,675.00
Qty 6+
₹38,976.00
Volume Pricing
Request Quote

Get Product Downloads



Coating:
AR Coating

Diameter (mm):
50.00

Extinction Ratio:
1000:1

Substrate:

Polymer Film on B270
Operating Temperature (°C): -25 to +65
Thickness (mm): 2.00
Thickness Tolerance (mm): ±0.2
Transmission (%): 30.00
Transmission Tolerance (%): ±3
Type: Linear Polarizer
Parallelism (arcmin): <4
Dimensional Tolerance (mm): +0.0/-0.2
Construction: Dichroic Polarizing Film on Glass
Wavelength Range (nm): 750 - 850

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View
