

TECHSPEC[®] 50mm Dia. x 100mm FL, 3-5μm Coated Germanium Meniscus Lens



Stock #87-966 [CONTACT US](#)

-

1

+

₹95,178.00

ADD TO CART

Qty 1-5
₹95,178.00
Qty 6+
₹76,142.00
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
50.00 +0.0/-0.1

Effective Focal Length EFL (mm):
100.00

Substrate: ☐
Germanium (Ge)

f/#:
2.00

Numerical Aperture NA: 0.25
Coating: BBAR (3000-5000nm)
Type: Meniscus Lens
Wavelength Range (nm): 3000 - 5000
Back Focal Length BFL (mm): 96.49
Center Thickness CT (mm): 5.00
Center Thickness Tolerance (mm): ±0.10
Centering (arcmin): <3
Clear Aperture (%): 90.00
Coating Specification: R _{avg} <3.0% @ 3 - 5µm
Edge Thickness ET (mm): 3.8
Focal Length Specification Wavelength (µm): 10.6
Radius R₁ (mm): 107.03
Radius R₂ (mm): 160.46
Surface Quality: 60-40
Wavelength Range (µm): 3 - 5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant