

TECHSPEC[®] 5.0mm Dia. x 15.0mm FL, NIR I, Inked, Plano-Convex Lens



Stock #48-713-INK 17 TO 22 D=DAYS

[Other Coating Options](#)

-

1

+

₹4,872.00

ADD TO CART

Qty 1-9
₹4,872.00
Qty 10+
₹4,394.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
5.00 ±0.025

Effective Focal Length EFL (mm):
15.00 @ 587.6nm

Back Focal Length BFL (mm): 13.94
Coating: NIR I (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 1.60 ±0.05
Edge Thickness ET (mm): 1.19
Radius R₁ (mm): 7.75
Clear Aperture CA (mm): 4.5
f/#: 3
Numerical Aperture NA: 0.17
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 600 - 1050
Damage Threshold, By Design: ☐ 7 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View