

TECHSPEC[®] 5.0mm Dia. x 20.0mm FL, Uncoated, Plano-Convex Lens



Stock **#49-873** 10 TO 12 DAYS
[Other Coating Options](#)

-

1

+

₹3,045.00

ADD TO CART

Qty 1-9
₹3,045.00
Qty 10+
₹2,741.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
5.00 +0.0/-0.025

Effective Focal Length EFL (mm):
20.00 @ 587.6nm

Back Focal Length BFL (mm): 19.02
Coating: Uncoated
Substrate:  N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 1.50 ±0.05
Edge Thickness ET (mm): 1.19
Radius R₁ (mm): 10.34
Clear Aperture CA (mm): 4.5
f#: 4
Numerical Aperture NA: 0.13
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 350 - 2200

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant
