

TECHSPEC® 50mm Dia x 50mm FL 3-5µm Coated, Ge Aspheric Lens



Stock **#87-996** 10 TO 12 DAYS
[Other Coating Options](#)

- 1 + **₹164,256.00**

ADD TO CART

Qty 1-5
₹164,256.00
Qty 6+
₹131,405.00
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
50.00 +0.0/-0.1

Effective Focal Length EFL (mm):
50.00 @ 4000nm

Numerical Aperture NA:
0.50

Back Focal Length BFL (mm):

45.92
Substrate: Germanium (Ge)
Aspheric Design Wavelength (nm): 4000
Asphere Figure Error, RMS @ 632.8nm: $\lambda/6$
Coating: BBAR (3000-5000nm)
Coating Specification: R_{avg} <3.0% @ 3 - 5μm
Centering (arcmin): ≤5
Surface Quality: 60-40
Clear Aperture CA (mm): 45
Edge Thickness ET (mm): 2.52
Center Thickness CT (mm): 5.10 ±0.10
f/#: 1.00
Bevel: Protective bevel as needed
Edges: Diamond Turned
Radius R₂ (mm): 62.38
Shape of Back Surface: Concave
Type: Aspheric Lens
Wavelength Range (nm): 3000 - 5000
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant