

TECHSPEC[®] 50mm Dia x -200mm FL, Protected Aluminum, Convex Mirror



Convex Mirrors

Stock #87-664 10 TO 12 DAYS

-

1

+

₹5,481.00

ADD TO CART

Qty 1-5
₹5,481.00
Qty 6+
₹4,394.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
50.00

Focal Length FL (mm):
-200.00

Center Thickness CT (mm):
5.00

Clear Aperture (%) 90.00
Coating: Protected Aluminum (400-700nm)
Coating Specification: R_{avg} >85% @400 - 700nm
Coating Type: Metal
Dimensional Tolerance (mm): +0.0/-0.1
Edge Thickness ET (mm): 4.21
Focal Length Tolerance (%): ±2
Radius R (mm): 400.0
Substrate: N-BK7
Surface Accuracy: λ/2
Surface Quality: 60-40
Thickness Tolerance (mm): ±0.1
Type: Spherical Mirror
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant