

TECHSPEC[®] 50mm Dia x -25mm FL, Enhanced Aluminum, Convex Mirror



Convex Mirrors

Stock #87-672

CONTACT US



1



₹6,134.00

ADD TO CART

Qty 1-5

₹6,134.00

Qty 6+

₹4,916.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
50.00

Focal Length FL (mm):
-25.00

Center Thickness CT (mm):
8.00

Clear Aperture (%) : 90.00
Coating: Enhanced Aluminum (450-650nm)
Coating Specification: R _{avg} >95% @450 - 650nm
Coating Type: Metal
Dimensional Tolerance (mm): +0.0/-0.1
Edge Thickness ET (mm): 1.30
Focal Length Tolerance (%) : ±2
Radius R (mm): 50.0
Substrate:  N-BK7
Surface Accuracy: λ/2
Surface Quality: 60-40
Thickness Tolerance (mm): ±0.1
Type: Spherical Mirror
Wavelength Range (nm): 450 - 650

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant