

50mm Diameter, Blue Dichroic Filter



Additive and Subtractive Dichroic Color Filters

Stock **#52-532** 10 TO 12 DAYS



1



₹3,437.00

ADD TO CART

Qty 1-24

₹3,437.00

Qty 25+

₹3,028.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
50.00

Angle of Incidence (°):
0

Cut-Off Wavelength (nm):
505.00

Substrate: 
Operating Temperature (°C): <100
Coating: Additive Color
Color: Blue
Surface Quality: 80-50
Thickness (mm): 2.00 Nominal
Type: Dichroic Filter
Dimensional Tolerance (mm): ±0.25
Clear Aperture (%): ≥85
Coating Specification: T _{avg} >85% @ 390 - 485nm, T _{avg} <1.0% @ 525 - 750nm T _{abs} >80% @ 400 - 485nm, T _{abs} <1.0% @ 620 - 690nm
Cut-Off Wavelength Tolerance (µm): 0.012

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant