


TECHSPEC® 50mm Enhanced Aluminum Coated, N-BK7 Right Angle Mirror



Stock **#45-689** 10 TO 12 DAYS

- 1 + **₹23,490.00**

ADD TO CART

Qty 1-5
₹23,490.00
Qty 6+
₹18,792.00
Volume Pricing
Request Quote

Get Product Downloads



Surface Flatness (P-V):
λ/4

Substrate: □
[N-BK7](#)

Surface Quality:
60-40

Length of Legs (mm):

50.00
Dimensional Tolerance (mm): ±0.1
Coating Specification: R _{avg} >95% @ 450 - 650nm
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Angle Tolerance (arcmin): ±2
Bevel: Protective bevel as needed
Clear Aperture CA (mm): 63.64 x 45.00
Length of Hypotenuse (mm): 70.70
Type: Right Angle Mirror
Wavelength Range (µm): 0.45 - 0.65
Wavelength Range (nm): 450 - 650
Damage Threshold, Reference: ☐ 0.2 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View