

TECHSPEC[®] 50mm H x 25mm L x 150mm FL Uncoated, Illumination Grade PCX Cylinder Lens



Stock #46-200 10 TO 12 DAYS

-

1

+

₹9,570.00

ADD TO CART

Qty 1-5
₹9,570.00
Qty 6+
₹7,656.00
Volume Pricing
Request Quote

Get Product Downloads



Effective Focal Length EFL (mm):
150.00

Substrate: N-BK7

f/#:
3

Numerical Aperture NA:

0.17
Coating: Uncoated
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): 146.51
Center Thickness CT (mm): 5.30
Center Thickness Tolerance (mm): ±0.1
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 50.0 x 25.0
Edge Thickness ET (mm): 1.17
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 77.78
Surface Quality: 60-40

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View