

50mm Square, 45° AOI, Hot Mirror



Hot Mirrors

Stock #43-957 10 TO 12 DAYS



1



₹4,785.00

ADD TO CART

Qty 1-9

₹4,785.00

Qty 10+

₹4,211.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Angle of Incidence (°):
45.00

Coating:
Hot Mirror, 45°

Substrate: ☐
[BOROFLOAT®](#)

Reflection (%):

>90, 750 - 1125nm
Dimensions (mm): 50.0 x 50.0
Surface Quality: 80-50
Thickness (mm): 3.30
Transmission (%): >85, 425 - 675nm
Type: Dichroic Filter
Dimensional Tolerance (mm): ±0.5
Coating Specification: Surface 1: 45° Hot Mirror Surface 2: None
Wavelength Range (nm): 425 - 1125
Surface Flatness (P-V): 4 - 6λ
Coating Type: Dielectric

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant