

50mm Square, Magenta Dichroic Filter



Additive and Subtractive Dichroic Color Filters

Stock **#39-913** 10 TO 12 DAYS



1



₹3,437.00

ADD TO CART

Qty 1-24

₹3,437.00

Qty 25+

₹3,028.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Dimensions (mm):
50.0 x 50.0

Angle of Incidence (°):
0

Cut-Off Wavelength (nm):
485.00

Cut-On Wavelength (nm): 615.00
Substrate:  BOROFLOAT®
Length (mm): 50.00
Operating Temperature (°C): <100
Coating: Subtractive Color
Color: Magenta
Surface Quality: 80-50
Thickness (mm): 2.00 Nominal
Type: Dichroic Filter
Width (mm): 50.00
Dimensional Tolerance (mm): ±0.25
Clear Aperture (%): ≥85
Cut-On Wavelength Tolerance (μm): 0.015
Coating Specification: T _{avg} >80% @ 380 - 470nm T _{avg} <1% @ 535 - 565nm T _{avg} >80% @ 655 - 750nm
Cut-Off Wavelength Tolerance (μm): 0.015

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant