

50mW, 532nm Fiber-Coupled Laser Module



Stock **#19-481** [CONTACT US](#)

-

1

+

₹69,600.00

ADD TO CART

Qty 1-9
₹69,600.00
Qty 10+
₹62,249.00
Volume Pricing
Request Quote

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads



Operating Temperature (°C):
+15 to +30

Operating Voltage (V):
5.0

Output Power (mW):
50

Spatial Mode: Fiber-Coupled
Wavelength (nm): 532.00 ±1
Length of Fiber (m): 1
Type of Laser: Diode
Laser Class - CDRH: Class IIIb
Color: Green
Connector: SMA
Length (mm): 151.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant
