

TECHSPEC® 50R/50T 50 x 50mm, UV Plate Beamsplitter



TECHSPEC® UV Plate Beamsplitters

Stock **#48-193** 10 TO 12 DAYS

⊖ 1 ⊕ **₹19,053.00**

ADD TO CART

Qty 1-5
₹19,053.00
Qty 6+
₹15,225.00
Volume Pricing
Request Quote

Get Product Downloads



Angle of Incidence (°):
45

Clear Aperture (%):
>85

Coating Specification:
Surface 1: R_{abs} = 50 ±5% @ 350nm, R_{avg} = 50 ±10%
over 250 - 450nm

T _{abs} =50 ±5% @ 350nm, T _{avg} = 50 ±10% over 250 - 450nm Surface 2: BBAR (R _{avg} <1%, R _{abs} <2% over 250 - 450nm)
Construction: Plate
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 50.0 x 50.0
Parallelism (arcmin): <5
Reflection/Transmission Ratio (R/T): 50/50
Substrate: ☐ Fused Silica (Corning 7980)
Surface Flatness (P-V): 1λ
Surface Quality: 60-40
Thickness (mm): 4.00
Thickness Tolerance (mm): ±0.38
Type: Standard Beamsplitter
Wavelength Range (nm): 250 - 450

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant