

TECHSPEC® 50R/50T VIS, C-Mounted Plate Beamsplitter



Stock **#49-685** 10 TO 12 DAYS

1

₹25,665.00

ADD TO CART

Qty 1-4
₹25,665.00
Qty 5+
₹22,533.00
Volume Pricing
Request Quote

Get Product Downloads

Coating Specification:
Surface 2: Multi-Layer Anti-Reflection for Visible Region

Construction:
Plate

Dimensional Tolerance (mm):
+0.0/-0.25

Extension Length (mm):

38.0
Housing: Black Anodized Aluminum
Housing Dimension: 38 x 38 x 50
Mount: C-Mount Enclosure
Reflection/Transmission Ratio (R/T): 50/50
Reflection/Transmission Tolerance (%): ±5
Substrate: ☐ N-BK7
Surface Flatness (P-V): 1λ
Surface Quality: 60-40
Thread Type: C-Mount (1" x 32 TPI)
Type: Standard Beamsplitter
Wavelength Range (nm): 400 - 700
Beamsplitter Included: #49-754

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant
