

50X Peak Direct Measuring Microscope



Peak Direct Measuring Microscopes

Stock **#39-111** CLEARANCE CONTACT US

-

1

+

₹28,710

ADD TO CART

Volume Pricing	
Qty 1-4	₹28,710 each
Qty 5+	₹27,270 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

Physical & Mechanical Properties

2.00

Field of View (mm):

At Focus: 41.5 Dia. x 122 L

Dimensions (mm):

0.02	Graduation (mm):
0 - 1.6	Reticle Scale (mm):
Up to 22	Depth Measurements (mm):
Optical Properties	
50X	Magnification:
11.7	Working Distance (mm):
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

Reticle should not be removed or replaced.

- Multiple Magnification Options
- Illuminated Models Available with English or Metric Reticles
- Removable Clear Acrylic Base

Peak Direct Measuring Microscopes are high power, portable microscopes designed for precise depth measurements. Peak Direct Measuring Microscopes feature a 10X focusable eyepiece and a scale with an accuracy of 0.1mm for measuring the length, width, or depth of an object. The clear cutaway acrylic base allows for manipulation of the sample while viewing. Illuminated models feature a removable pen illuminator, and include two AA batteries. Peak Direct Measuring Microscopes are sold with a hard-shell vinyl storage case.

Note: Reticle should not be removed or replaced.