

[See all 6 Products in Family](#)

52 x 120mm, White, EuroBrite™ Ring Light

See More by [Advanced Illumination](#)



All EuroBrite Ring Light



Stock #33-447 **1 In Stock**

MRP ₹33,984

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹33,984 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General

50,000 **Operating Lifetime (hours):**

RL-S052120MWHI **Model Number:**

LED Illuminator **Type of Illumination:**

See Technical Information Tab for Typical Intensity **Note:**

Advanced Illumination **Manufacturer:**

Ring Light **Geometry:**

Strobed or Constant **Illumination Mode:**

Physical & Mechanical Properties

120 x 120 x 30 **Dimensions (mm):**

173.00 **Weight (g):**

Optical Properties

White **Color:**

Electrical

0.42 - 0.49A **Maximum Input Current:**

10% @ 0.7V, 100% @ 10V **Analog Intensity Control:**

10µm **Trigger-to-Pulse Latency:**

Hardware & Interface Connectivity

Flying Leads **Connector:**

24V nominal (min. 22 / max. 28) **Input Voltage (V):**

Power Supply:
Power Supply Required and Sold Separately.
USA: [#66-855](#)
Europe: [#66-855](#)
Japan: [#89-513](#)
Korea: [#33-773](#)
China: [#66-855](#)

Environmental & Durability Factors

0 - 60 **Operating Temperature (°C):**

IP67 **Environmental Rating:**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Contains SVHC\(s\)](#) **Reach 233:**

United States **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- 52mm Inner Diameter
- Requires No Heat Sink
- Available in White, Red, and Blue

Advanced Illumination EuroBrite™ Ring Light illuminators feature on-board smart drivers functional during strobe and continuous operation modes making them ideal for the most demanding performance constraints. Adaptive OverDrive™ allows for power optimization while in strobing mode, and Adaptive Thermal Feedback™ gives operational current control to the user, preventing overheating and eliminating the need for a heat sink. These Advanced Illumination EuroBrite™ Ring Light illuminators feature a ruggedized, sealed enclosure, and are available in white, red, or blue versions. The illuminators inner diameter can accommodate components up to 52mm in diameter. An analog dimming control operable in both strobe and continuous modes add to illuminator's customizability.

Note: A24V power supply is required.

Technical Information

Typical Intensity			
Working Distance	200mm	300mm	600mm
Area	ø132mm	ø145mm	ø226mm
Typical Irradiance (W/m ²)	100.0	74	28
Typical Illuminance (kLux)	34.0	25	10

;