

TECHSPEC® 532 & 1064nm, 50mm Dia., OD 6.0 Multi-Notch Filter



TECHSPEC OD 6.0 Multi-Notch Filters for Nd:YAG Lasers

Stock **#87-025** 10 TO 12 DAYS
[Additional Bandwidths](#)

- 1 + **₹185,745.00**

ADD TO CART

Qty 1-5
₹185,745.00
Qty 6+
₹148,596.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
50.00 +0.00/-0.10

Optical Density OD (Average):
≥6.0

Center Wavelength CWL (nm):
532.00 & 1064

Full Width-Half Max FWHM (nm): 25.00 @ 532nm 50 @ 1064nm
Coating: Hard Coated
Surface Quality: 60-40
Thickness (mm): 3.50
Thickness Tolerance (mm): ±0.1
Transmission (%): >80 avg @ 325 - 400nm >90 avg @ 400 - 1200nm
Transmission Wavelength (nm): 325 - 1200
Type: Notch Filter
Construction: Mounted in Black Anodized Ring
Clear Aperture (%): >85
Durability: ML-C-48497A
Reflection at CWL (%): >99.5
Transmitted Wavefront, RMS: 1λ

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant