

532nm Flat Top Beam Shaper | πShaper 12_12_532_HP

See More by [AdlOptica](#)



Stock **#15-496** [CONTACT US](#)

- 1 + **₹765,687.00**

ADD TO CART

Qty 1-4
₹765,687.00

Qty 5+
₹689,127.00

Volume Pricing
Request Quote

Get Product Downloads

Design Wavelength DWL (nm): 532
Diameter (mm): 42.00
Entrance Beam Diameter, 1/e² (mm): 12.0 - 12.1
Model Number:

πShaper 12_12_532_HP
Length (mm): 358.00
Mounting Threads: M27 x 1
Type: Beam Shaper
Weight (g): <530
Wavelength Range (nm): 515 - 550
Style: Flat Top
Damage Threshold, By Design: ☐ 3 J/cm² @ 5ns (typical)
Output Diameter, FWHM (mm): 11.8

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant