

55mm Focal Length Partially Telecentric Video Lens



55mm Focal Length Partially Telecentric Video Lens, #52-271

Stock **#52-271** 10 TO 12 DAYS

⊖ 1 ⊕

₹60,465.00

ADD TO CART

Qty 1+
₹60,465.00
Volume Pricing
Request Quote

Get Product Downloads

Iris Option:
Variable

Horizontal Field of View, 1/2" Sensor:
Non-Telecentric: 12.8mm - 6.7°
Telecentric: 12.8 - 16.0mm

Filter Thread:
M43 x0.75

Weight (g):
314.68

Maximum Image Circle (mm):

11.00
Note: PMAG: Non-Telecentric: 0.5X - 0X Telecentric: 0.5X - 0.4X Working Distance (mm): Non-Telecentric: 127 - ∞ Telecentric: 127 - 158.75
Type: Telecentric Lens
Focal Length FL (mm): 55.00
Primary Magnification PMAG: 0.5X - 0.4X
Maximum Sensor Format: 2/3"
Working Distance (mm): 127 - 158.75
Mount: C-Mount
Aperture (f/#): f/2.8 - f/32
Distortion (%): <1.0
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View