

5.6" Diagonal LCD Flat Panel Monitor



Stock **#55-786** CLEARANCE 10 TO 12 DAYS

- 1 + **₹13,045.65**

ADD TO CART

Qty 1+
₹13,045.65

Volume Pricing
Request Quote

Get Product Downloads

Type: Monitor
Resolution (MegaPixels): 0.20
Pixels (H x V): 960 x 234
Power Supply: 100 - 240 VAC Included
Power Consumption (W): <7

Dimensions (mm): 133 W x 160 H x 37 D
Dot Pitch (mm): 0.119 x 0.357
Size of Screen, Diagonal (inches): 5.6
Maximum Viewing Angle, MVA (°): 45 Left/Right, 10 Up/Down
Weight (kg): 0.458
Input/Output Options: Mini Phone Jack (RCA Adapter Included)/ No Output Terminals
Active Area (mm): 113.3 H x 84.7 W
Signal Format: NTSC/ PAL
Contrast: 150:1
Brightness (cd/m²): 200
Response Time (ms): 35
Safety Standards: FCC

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View