

# 590nm, LED Linear Axial Diffuse Light

See More by [Advanced Illumination](#)



Stock **#66-876** [CONTACT US](#)

- 1 + **₹287,970.00**

ADD TO CART

|             |
|-------------|
| Qty 1+      |
| ₹287,970.00 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

**Note:** This item requires accessories for use | [Learn More](#)

Get Product Downloads

|                                               |
|-----------------------------------------------|
| <b>Color:</b><br>Yellow                       |
| <b>Model Number:</b><br>DL110-590-IC          |
| <b>Operating Temperature (°C):</b><br>0 to 60 |
| <b>Wavelength (nm):</b><br>590.00             |

|                                                                                                                                                                                                                                             |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Weight (lbs):</b><br>1.3                                                                                                                                                                                                                 |
| <b>Working Distance (mm):</b><br>12.7 - 50                                                                                                                                                                                                  |
| <b>LED Lifetime (hours):</b><br>50,000                                                                                                                                                                                                      |
| <b>Power Supply:</b><br>Power Supply Required and Sold Separately.<br>USA: <a href="#">#66-855</a><br>Europe: <a href="#">#66-855</a><br>Japan: <a href="#">#66-855</a><br>Korea: <a href="#">#33-773</a><br>China: <a href="#">#66-855</a> |
| <b>Light Distribution (%):</b><br>±10                                                                                                                                                                                                       |
| <b>Number of LEDs:</b><br>12 High Brightness                                                                                                                                                                                                |
| <b>Length of Cable (m):</b><br>2                                                                                                                                                                                                            |
| <b>Maximum Trigger Frequency (Hz):</b><br>30.00                                                                                                                                                                                             |
| <b>Strobe Duration (µs):</b><br>30 - 300                                                                                                                                                                                                    |
| <b>Type of Illumination:</b><br>LED Illuminator                                                                                                                                                                                             |
| <b>Note:</b><br>Requires a 24V power supply <a href="#">#66-855</a> . European power supply <a href="#">#35-200</a> also available.                                                                                                         |
| <b>Manufacturer:</b><br>Advanced Illumination                                                                                                                                                                                               |
| <b>Geometry:</b><br>Diffuse Axial                                                                                                                                                                                                           |
| <b>Illumination Mode:</b><br>Constant                                                                                                                                                                                                       |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |