

TECHSPEC[®] 5mm Dia. x 25mm FL, VIS-EXT Coated, Double-Convex Lens



Stock **#89-128** 10 TO 12 DAYS
[Other Coating Options](#)

-

1

+

₹4,524.00

ADD TO CART

Qty 1-9
₹4,524.00
Qty 10+
₹4,067.00
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
5.00 +0.000/-0.025

Back Focal Length BFL (mm):
24.5

Effective Focal Length EFL (mm):

25.00
Coating: VS-EXT (350-700nm)
Coating Specification: R _{avg} <0.5% @ 350 - 700nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <3
Bevel: Protective bevel as needed
Center Thickness CT (mm): 1.50
Center Thickness Tolerance (mm): ±0.05
Edge Thickness ET (mm): 1.26
Radius R₁=R₂ (mm): 25.58
Clear Aperture CA (mm): 4.5
f/#: 5.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.10
Type: Double-Convex Lens
Wavelength Range (nm): 350 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant