

TECHSPEC® 5mm Dia x 8mm FL MgF₂ Coated, Illumination Grade PCX Cylinder Lens



Stock #47-760

10 TO 12 DAYS

-

1

+

₹10,266.00

ADD TO CART

Qty 1-5
₹10,266.00
Qty 6+
₹8,222.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
5.00

Effective Focal Length EFL (mm):
8.00

Substrate:

N-BK7

f/#:

1.6
Numerical Aperture NA: 0.31
Coating: MgF ₂ (400-700nm)
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 400 - 700
Back Focal Length BFL (mm): 5.72
Center Thickness CT (mm): 3.00
Center Thickness Tolerance (mm): ±0.1
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Dimensional Tolerance (mm): +0.0/-0.2
Edge Thickness ET (mm): 2.12
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 4.13
Surface Quality: 60-40
Tilt Tolerance (mm): ±0.1 over H
Typical Applications: 10 J/cm ² @532nm, 10ns
Wedge Tolerance (arcmin): 15.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant
